

Reverse Osmose

Capaciteit 3000 - 3500 l/h



KR and KR/FU Series: 3000 – 3500 l/h RO Systems with special concentrate stage

Stand-type unit for desalination of softened drinking water according to German drinking water regulations (free chlorine not detectable), operating on the principle of reverse osmosis, with very high permeate recovery up to 90 % due to additional concentrate stage and high salt rejection up to 98.5 %.

With controller RO 5000 and horizontal 8'' membranes as well as concentrate rinsing unit, connection set for manual cleaning device. Picture UO 4000 KR.



Advantages of the KR series:

- Water saving system through additional concentrate stage: Permeate yield up to 90%
- ROI / payback period < 1 year through cost savings in water, wastewater and energy *
- High Salt rejection rate: 98,5%
- Very low energy consumption for KR/FU systems, complies with IE 3

* assumed cost for water, waste water and energy of 1 €/m³, 2 €/m³, 0,12 €/kWh and system use of 4000 h/year, comparing a KR/FU with a standard ND type system.

Geonwater BV Centaurusweg 148-02 TILBURG
T. +31 (0)13 533 44 69 E. geon@geonwater.nl

www.geonwater.nl

KR and KR/FU series

Unit design Stainless steel main frame housing the instruments and controls.

Special inlet filter with 5 µm-filter cartridge, **high pressure pump** low noise (incl. frequency converter for KR/FU systems), multi-stage centrifugal type, **specially combined spirally wound modules** with PA/PS composite membranes in GRP vessels with inliner.

Valves such as sampling valves for feed water and permeate (for each pressure vessel), KR-permeate recirculation, inlet solenoid/diaphragm valve, valves made of stainless steel to regulate the flow rate of permeate, concentrate and concentrate recirculation.

Pressure gauges for inlet and outlet pressure pre-filter, pump pressure, operating pressure and concentrate pressure, pressure switch for monitoring the feed water pressure.

Flow meters for permeate, KR-permeate recirculation, concentrate and concentrate recirculation flow rate.

Conductivity measurement permeate and KR-permeate recirculation, temperature compensated, measuring ranges 2-200 µS/cm and 20-2,000 µS/cm.

Connection set for manual cleaning device and concentrate flushing device

Control cabinet with lockable main switch, electrical switchgear for control of the high-pressure pump.

Unit is completely wired, pre-assembled and ready for installation. Electrical equipment in accordance with VDE 0100 part 600, VDE part 1.



RO 5000 microprocessor control system for fully automated monitoring and control of the reverse osmosis unit with graphics display with scrollable display (selectable) of **operating data:** permeate- and feed-water conductivity (temperature compensated), permeate- and feed-water temperature, operating hours, time **malfunction signals:** low pressure, hard water, motor overload, high conductivity prealarm (permeate), high conductivity fault (permeate), **status signals:** operation, permeate discard/ permeate recycling, concentrate displacement, concentrate rinse, intermittent rinse during shut down, shut down by external signal (forced stop, regeneration), tank full, **LEDs** for operation, malfunction.

Chip card reader for storage of parameters and data (1 chip card is included in our scope of delivery), RS232 interface.

Additional connections possible: **Inputs** (low voltage) for level control with 1 or 2 float switches, hardness monitoring unit (the RO 5000 control system includes control functions for the limitron hardness monitoring unit), shut-down by external signal (forced stop, regeneration. **Outputs** additional pump (in series or duty/standby) for 2 solenoid valves for concentrate rinse, permeate discard and recycling, collective malfunction, prealarm high conductivity and freely programmable universal output each on floating changeover contact, analogue output of permeate conductivity and permeate temperature (4-20 mA).

The units are designed for a maximum TDS of 1,000 mg/l, a max. SiO₂-concentration of 10 mg/l, a water temperature of 15°C, a maximum colloidal index of 3 and free permeate outlet. Under these conditions, the units still reaches design permeate flow after three years of operation. The permeate recovery depends on the raw water quality and the type of pre-treatment.

Technical Data KR + KR/FU		UO 3000	UO 3500
Permeate flow rate	l/h	3000	3500
Min. salt rejection	%	98,5	98,5
Recovery	%	85	85
Operating pressure	bar	18,5	18
Membrane element / number		4040/12	4040/14
Voltage	V/Hz	3 x 400/50	3 x 400/50
Motor power	kW	5,5	5,5
Pre-fusing	A	16	16
Feedwater connection	DN	32	32
Permeate/concentrate connection	DN	25/25	25/25
Conductivity permeate	µS/cm	2 - 200	2 - 200
Cond. Permeate recirculation	µS/cm	20 - 2,000	20 - 2,000
Height	mm	1.650	1.650
Width	mm	3.550	3.550
Depth	mm	700	700
Weight approx	kg	400	450

Min./max. feed water pressure 2/4 bar, Min./max. feed water temperature 5/25 °C, Max ambient temperature 40 °C, pH 3-11

Geonwater BV Centaurusweg 148-02 TILBURG
T. +31 (0)13 533 44 69 E. geon@geonwater.nl

www.geonwater.nl

